


AC/DC CURRENT CLAMP

E27 model (isolated AC/DC current sensor)


Curves

100 A calibre

DC linearity



AC linearity




10 A calibre


100 A calibre

Frequency response

Typical frequency response at 0.5 A E27 clamp with 100 mV/A calibre




Typical frequency response at 1 A E27 clamp with 10 mV/A calibre



Frequency phase shift

Frequency-dependent phase shift at 1 A E27 clamp with 100 mV/A calibre



Frequency-dependent phase shift at 1 A E27 clamp with 10 mV/A calibre

